

PAWS

RESERVDELAR



REHASENSE




INFORMATION

ORDERFORMULÄR

| | |
|----------------|------------------|
| Företag : | Datum: |
| | Order nr: |
| Kontaktperson: | Leveransadress |
| E-Mail: | Gata: |
| Tel./Fax: | Postnr. och ort: |

TECHNICAL DRAWING FOR PAWS



| No. | Bild | Beskrivning | Art. nr. | Antal |
|-----|---|---|-----------|-------|
| 1 |  | Panasonic, Lithiumbatteri ZZ991304, 48 V, 11.6 AH | EBB0048-A | |
| 2 |  | Batterihållare, ZZ991304 (cable length = 120 mm including plug) | EBB0048-2 | |
| 3A |  | Lampa, Albert, 48 V, SPL- 01, high beam: 1900LM / 40 W, kabel L = 450 mm | EBE002 | |
| 3B |  | Lampa, Albertx, 48 V, SPL-01, High kabel L = 150 mm | EBE002-12 | |
| 4A |  | Standarddäck City 12" | 431207 | |
| 4B |  | Standarddäck City 14" | 440872 | |
| 4C |  | Standarddäck Cruiser 16" | 431603 | |
| 4D |  | Standarddäck Tourer 20" X 2.125" | 432007 | |
| 4E |  | Standarddäck Tourer 20" X 4.0" | 432005 | |
| 4F |  | Alternativt däck för 14" PAWS Grovt däck med upphöjt mönster 3.50"- 8", | 440806 | |
| 4G |  | Alternativt däck för 16" PAWS Crossdäck 80/100-12", svart | 431296 | |
| 4H |  | Alternativt däck 1 för 20" PAWS CS däck 3.50 - 16" med förhöjt mönster C-7201 | 43200C | |
| 4A |  | Slang standard City 12" | 451214 | |
| 4B |  | Slang standard City 14" | 450811 | |
| 4C |  | Slang standard Cruiser 16" | 451602 | |
| 4D |  | Slang standard Tourer 20" X 2.125" | 45200A | |
| 4E |  | Slang standard Tourer 20" X 4.20" | 452000 | |

PAWS RESERVDELAR

| | | | | |
|-----------|---|--|----------|--|
| 4F |  | Slang 3.50"-8" med bilventil 45/90 | 45080B | |
| 5A |  | Shimano RT66 bromsskiva D203MM för PAWS | 69D00N | |
| 5B |  | Shimano RT56 bromsskiva D160MM för PAWS | 69D00K | |
| 6 |  | Bromsok för skivbroms, Zoom DB-330 vänster och höger | 69D00-RS | |

| No. | Bild | Beskrivning | Art. nr. | Antal |
|-----|---|---|------------|-------|
| 7A |  | Side bracket, left Pins L = 107 mm, with black clamp for Mclamp | EBC107L-BK | |
| 7B |  | Side bracket, left Pins L = 150 mm, with black clamp for Mclamp | EBC150L-BK | |
| 7C |  | Side bracket, left Pins L = 190 mm, with black clamp for Mclamp | EBC190L-BK | |
| 8A |  | Manual clamp for PAWS, without safety lock, left side, silver anodized | EBC00F-SL | |
| 8B |  | Electric clamp for PAWS, with 24 V / 110 RPM / 27 Nm motor, Left side, Silver | EBD01A-SL | |
| 9A |  | Support leg subassembly left for 12 inch | EBL00S | |
| 9B |  | Support leg subassembly left for 14 inch | EBL00S | |
| 9C |  | Support leg subassembly left for 16 inch | EBL00K | |
| 9D |  | Support leg subassembly left for 20 inch | EBL00P | |
| 10A |  | Mudguard Black, for 12 inch | EBF102B-RS | |
| 10B |  | Mudguard Black, for 14 inch | EBF102B-RS | |
| 10C |  | Mudguard Black, for 16 inch | EBF104B-RS | |
| 10D |  | Mudguard Black, for 20 X 4.0 inch | EBF103B-RS | |
| 11A |  | Side bracket, right pins L = 107 mm, with black clamp | EBC107R-BK | |
| 11B |  | Side bracket, right pins L = 150 mm, with black clamp | EBC150R-BK | |
| 11C |  | Side bracket, right pins L = 190 mm, with black clamp | EBC190R-BK | |
| 12 |  | Sleeve for Manual PAWS Clamp, Alu. 6061-T6, D51 ,5 x L18 Black anodized | EBC045-BK | |

| No. | Bild | Beskrivning | Art. nr. | Antal |
|-----|---|---|-----------|-------|
| 13 |  | QR handle for manual central lift unit, aluminum with bolt | EBAT15-RS | |
| 14A |  | Manual clamp for PAWS, without safety lock, Right side, Silver anodized | EBC00E-SL | |
| 14B |  | Electric clamp for PAWS, with 24 V / 110 RPM / 27 Nm motor, Right side, Silver | EBD01B-SI | |
| 15A |  | Support leg subassembly right for 12 inch | EBLOOT | |
| 15B |  | Support leg subassembly right for 14 inch | EBLOOT | |
| 15C |  | Support leg subassembly right for 16 inch | EBL00L | |
| 15D |  | Support leg subassembly right for 20 inch | EBL00Q | |
| 16 |  | Brake pad for brake caliper, set of 2 | 69D00U-RS | |
| 17 |  | Handlebar grip | EBE00L-RS | |
| 18 |  | Tetra foam handle assembly 3 pieces in set | EBH00E-RS | |
| 19 |  | Handlebar, aluminum, D22 x 1.5, L = 480 mm, black | EBH002 | |
| 20 |  | Display for PAWS, IMPORTANT: Before shipping, the display must be re-programmed with the latest software and the dealer's own login + setting profile must be set as usual. | EBE000 | |
| 21 |  | Sticker for buttons | EBS541-RS | |
| 22 |  | Parts for extension bar | EBF021-RS | |
| 23 |  | 4 Switch unit for PAWS, DK2402, D22 mm, cable L = 200 mm, 7PIN, with JL-F-710AG connector | EBE004-A | |
| 24 |  | Tester for lamp SPL-1, DK138/2, with EBE016-2F (JL-F-Z208M), waterproof cable, L = 200 mm | EBE011 | |
| 25 |  | Speed mode button + Power switch, FOR DISPLAY | EBE000-S | |
| 26 |  | Throttle + 3 buttons, S4301 + HT390. (Cruise/TC/Walk) for PAWS, cable L = 200 mm | EBE00H-S | |

| No. | Bild | Beskrivning | Art. nr. | Antal |
|-----|---|--|------------|-------|
| 27 |  | Cable with changeover switch for manual lift system for PAWS | EBA142 | |
| 28 |  | Spiral cable with 2-sided 5-wire waterproof plug for E-Clamp | EBE011C | |
| 29 |  | Brake L: D7.0 x 1050 mm / inner L:D1.5 x 890 mm, STD | 69104D | |
| 30 |  | Brake L: D5.0 x 1070 mm / inner L:D1.5 x 890 mm, Tetra | 69103O | |
| 31 |  | Integrated waterproof cable, 10PIN | EBE00B-4 | |
| 32 |  | Battery holder with 3 keys | EBE0048-KU | |
| 33 |  | Lamp holder | EBE002-B | |
| 34 |  | PAWS actuators 45mm stroke length | 94RA65A | |
| 35 |  | PAWS actuators 38mm stroke length | 94RA66A | |



Flottiljvägen 19
SE-392 41 Kalmar | Sweden
M: +46 722 325 090
E: info@wihlbackamobility.se
W:wihlbackamobility.se

Rehasense's quality management complies with both the ISO 9001 and ISO 13485 standards, as confirmed by TÜV NORD.
Rehasense's medical devices are CE-marked and meet the requirements of EU Regulation 2017/745 (MDR).
Copyright Rehasense® 2022

